SIEMENS

Data sheet

6EP4438-7EB00-3DX0

SITOP SEL1400 SELECTIVITY MODULE 8* 10A SITOP SEL1400 10 A Selectivity module 8-channel with limiting characteristic Input: 24 V DC/60 A output: 24 V DC/8x 10 A Threshold adjustable 2-10 A with monitoring interface



| Input | |
|---|-----------------------|
| Type of the power supply network | Controlled DC voltage |
| Supply voltage / at DC / Rated value | 24 V |
| Input voltage / at DC | 20.4 30 V |
| Overvoltage overload capability | 35 V |
| Input current / at rated input voltage 24 V / Rated value | 60 A |
| Outout | |

| Output | |
|--|--|
| Voltage curve / at output | controlled DC voltage |
| Formula for output voltage | Vin - approx. 0.2 V |
| Relative overall tolerance / of the voltage / Note | In accordance with the supplying input voltage |
| Number of outputs | 8 |
| Output current / up to 60 °C / per output / rated value | 10 A |
| Adjustable pick-up value current / of the current- dependent overload release | 2 10 A |
| Type of response value setting | via potentiometer |
| Product feature / parallel switching of outputs | Yes |
| Product feature / bridging of equipments | No |

| Туре с | f outputs | connection |
|--------|-----------|------------|
|--------|-----------|------------|

Connection of all outputs after ramp-up of the supply voltage > 20 V; delay time of 25 ms, 200 ms, 500 ms or "load-optimized" can be set via DIP switch for sequential connection

| Efficiency | |
|--|--|
| Efficiency in percent | 99 % |
| Power loss [W] / at rated output current / for rated value of the output current / typical | 15 W |
| Switch-off characteristic per output | |
| Switching characteristic | |
| of the excess current | lout = 1.01.5 x set value, switch-off after approx. 5 s |
| of the current limitation | lout = 1.5 x set value, switch-off after typ. 100 ms |
| of the immediate switch-off | lout > set value and Vin < 20 V, switch-off after approx. 0.5 ms |
| Design of the reset device/resetting mechanism | via sensor per output |
| Remote reset function | Non-electrically isolated 24 V input (signal level "high" at > 15 V) |
| Protection and monitoring | |
| Fuse protection type / at input | 20 A fast per output (not accessible) |
| Display version / for normal operation | Three-color LED per output: green LED for "Output switched through"; orange LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent" |
| Design of the switching contact / for signaling | Floating status signal output (pulse/pause signal that can be |
| function | evaluated via SIMATIC function block) |
| Safety | |
| Galvanic isolation / between input and output at switch-off | No |
| Operating resource protection class | Class III |
| Certificate of suitability | |
| CE marking | Yes |
| Standard / for safety | according to EN 60950-1 and EN 50178 |
| Protection class IP | IP20 |
| EMC | |
| Standard | |
| • for emitted interference | EN 61000-6-3 |
| for interference immunity | EN 61000-6-2 |
| Operating data | |
| Ambient temperature | |
| • during operation | -25 +70 °C |
| — Note | with natural convection |
| • during transport | -40 +85 °C |
| • during storage | -40 +85 °C |
| Environmental category / acc. to IEC 60721 | Climate class 3K3, 5 95% no condensation |
| | |

Mechanics

| Type of electrical connection | Push-in |
|--|---|
| ● at input | 24V1, 24V2: push-in for 0.75 16 mm ² ; 0V1, 0V2: push-in for 0.2 4 mm ² |
| • at output | 1 - 8: push-in for 0.2 4 mm ² |
| for signaling contact | 13, 14: push-in for 0.2 1.5 mm ² |
| for auxiliary contacts | RST: push-in for 0.2 1.5 mm ² |
| Width / of the enclosure | 45 mm |
| Height / of the enclosure | 135 mm |
| Depth / of the enclosure | 125 mm |
| Installation width | 45 mm |
| Mounting height | 225 mm |
| Net weight | 0.5 kg |
| Mounting type | Snaps onto DIN rail EN 60715 35x7.5/15 |
| MTBF / at 40 °C | 363 000 h |
| Other information | Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified) |