

Angle grinder WE 15-125 Quick

1550 watt

metabo[®]

Execution:

- Cut-out carbon brushes protect the motor
- Metabo S-automatic: mechanical safety coupling
- Tacho-Constamatic (TC) full-wave electronics: consistent rotation speed under load for good work progress

Delivery:

Protective cover, support flange, M-Quick clamping nut, extra VibraTech (MVT)handle



Art. no.	70373 298
Brand	METABO
Manufacturer Part Number	600448000
Model	WE 15-125 Quick
Manufacturer Article Number	600448000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1550 W
Power output	940 W
Idle speed	11000 rpm
Thread dimension of spindle	M14
Weight	2.5 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	Yes
With reverse switch off	Yes
With disc brake	No
With quick clamping system	Yes
With dead man function	No
Gross Weight	3.560 kg
Product Group	745

EAN

4007430245496