

TEGERA® 8802 INFINITY

Synthetic glove, nitrile, nitrile foam/waterbased PU, palm-dipped, double-dipped, nylon, spandex, 18 gg, foam grip pattern, Cat. II, black, yellow, withstands contact heat up to 100°C, oil and grease resistant palm, waterproof palm, for assembly work

PROPERTIES

High level of protection, good fingertip sensitivity, flexible, durable, good grip in oily environments, extra comfortable

SPECIFICATION

TYPE OF GLOVE Work gloves - General handling

CATEGORY Cat. II

SIZE RANGE (EU) 5, 6, 7, 8, 9, 10, 11

COLLECTION Infinity

LINER MATERIAL Nylon, spandex, 18 gg

DIPPING Palm-dipped, double-dipped

DIPPING MATERIAL Nitrile, nitrile foam/waterbased PU

DEXTERITY 5

GRIP PATTERN Foam grip pattern

CUFF STYLE Knitwrist cuff

COLOUR Black, yellow

PAIRS PER PACKAGE/CARTON 6/120

DISPLAY Hook

MATERIAL SPECIFICATION Nitrile, nylon, elastane



I N F I N I T Y™



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

TEGERA® 8802 INFINITY

FEATURES

Withstands contact heat up to 100°C, approved for handling foodstuffs, oil and grease resistant palm, anatomically designed

PREVENTS RISK OF

Abrasion injuries, blisters, grazes, scratches, lacerations, contact with dirt, drying out, chapping, contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Dry environments, wet environments, moist environments, oily and greasy environments, dirty environments

PRIMARY AREAS OF USE

Fine assembly, assembly, machine operating, building and construction, carpentry, installation work, HVAC installation, engineering, transport work, machine driving, warehouse work, airport work, repair work, service work, shop work

PRIMARY INDUSTRIES OF USE


Machinery and equipment, MRO, automotive, transportation, utilities, building and construction, logistics, facilities, service, retail

TYPE OF WORK

Medium weight



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

2(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

TEGERA® 8802 INFINITY

EC TYPE EXAMINATION

Notified Body: 0075 CTC, 4 rue Hermann Frenkel, 69367 Lyon Cedex 07 France

COMPLIANCE DESCRIPTION

EN 420:2003 + A1:2009 Protective gloves - general requirements and test methods

EN 388:2003 Protective gloves against mechanical risks

Property	Level Achieved	(Maximum Performance)
A) Resistance to abrasion (No. of revolutions)	4	(4)
B) Resistance to cutting (Index)	1	(5)
C) Tear resistance (Newton)	2	(4)
D) Puncturing resistance (Newton)	1	(4)

EN 388 - Testing (specifies the requirements that apply for each safety level).


Level of protection/Performance level	1	2	3	4	5
A) Resistance to abrasion (No. of revolutions)	100	500	2 000	8 000	
B) Resistance to cutting (Index)	1,2	2,5	5,0	10,0	20,0
C) Tear resistance (Newton)	10	25	50	75	
D) Puncturing resistance (Newton)	20	60	100	150	

EN 407:2004 Protective gloves against thermal risks (heat and/or fire)

CONFIDENCE IN TEXTILES Tested for harmful substances according to Oeko-Tex® Standard 100



CE Cat. II



All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2018-05-14

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com