

## Combination spanner (DIN 3113 B)

DIN 3113 B, jaw angle 15°, ring side flat with depressed centre

**ATORN**

### Execution:

- With completely new special surface
- Maximum resistance against contact corrosion
- 15x greater corrosion protection against exposure to temperature, road salt and environmental influences compared to conventionally coated keys
- Up to 720 hours in the salt spray test in accordance with DIN EN ISO 9227
- Environmentally friendly chromium-VI-free coating process
- Made from chromium-vanadium steel, die-forged and hardened.
- DIN 3113 B

### Advantage:

- Extremely durable and robust industrial design



<b>Art. no.</b>	<b>52039 108</b>
<b>Brand</b>	ATORN
<b>Manufacturer Part Number</b>	50066106
<b>Tip type</b>	Twelve-sided head
<b>Width across flats</b>	8 mm
<b>Length</b>	125 mm
<b>Tip profile type</b>	ENERGY profile
<b>Jaw position</b>	15 Degree
<b>Surface</b>	Special coating according to specifications
<b>Material</b>	Chrome-vanadium steel
<b>DIN</b>	3113
<b>Gross Weight</b>	0.028 kg
<b>Product Group</b>	5HB

### Main EAN Code

4050293537208

