

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Date of issue: 23/11/2018 Revision date:

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### **Product identifier**

Product form : Mixture Product name : TYRE FOAM Product code 15123 Vaporizer : Aerosol

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.2.1 Relevant identified uses

Intended for general public

Main use category : Consumer use

Use of the substance/mixture : Automotive Care Products.

#### Uses advised against 122

No additional information available

#### Details of the supplier of the safety data sheet

Turtle Wax Europe Limited 4th Floor Alaska House, Atlantic Park, **Dunnings Bridge Road** Liverpool, L30 4AB - United Kingdom T +44 151 530 4740

MSDS@turtlewaxeurope.com

#### **Emergency telephone number**

: +44 151 530 4740 Emergency number

Office hours only 08:30 - 17:00

### **SECTION 2: Hazards identification**

## Classification of the substance or mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol 1 H222;H229 Eye Irrit. 2 H319 Skin Sens. 1 H317

Full text of H statements : see section 16

## **Label elements**

Signal word (CLP)

## Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)





: Danger

Hazardous ingredients : BENZISOTHIAZOLINONE

Hazard statements (CLP) : H222 - Extremely flammable aerosol.

H229 - Pressurised container: May burst if heated. H317 - May cause an allergic skin reaction. H319 - Causes serious eye irritation.

Precautionary statements (CLP) : P102 - Keep out of reach of children.

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No

smoking.

P211 - Do not spray on an open flame or other ignition source.

P251 - Do not pierce or burn, even after use. P280 - Wear protective gloves, eye protection. P302+P352 - IF ON SKIN: Wash with plenty of water.

P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.

P333+P313 - If skin irritation or rash occurs: Get medical advice/attention.

23/11/2018 EN (English) 1/8

Version: 1.0

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

P337+P313 - If eye irritation persists: Get medical advice/attention.

P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C. P501 - Dispose of contents / container in accordance with local / national regulations.

#### 2.3. Other hazards

Adverse physicochemical, human health and environmental effects

: Pressurised container: May burst if heated. Extremely flammable aerosol. Causes skin irritation. Causes serious eye irritation.

#### **SECTION 3: Composition/information on ingredients**

#### 3.1. Substances

Not applicable

#### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Longchain alkoxylated alcohol C10 polymer	(CAS-No.) 166736-08-9	1 - 10	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
Longchain alkoxylated C10 polymer	(CAS-No.) 166736-08-9	1 - 10	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
BENZISOTHIAZOLINONE	(CAS-No.) 2634-33-5 (EC-No.) 220-120-9 (EC Index-No.) 613-088-00-6	0.1 - 1	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Dam. 1, H318 Skin Sens. 1, H317 Aquatic Acute 1, H400
sodium nitrite	(CAS-No.) 7632-00-0 (EC-No.) 231-555-9 (EC Index-No.) 007-010-00-4 (REACH-no) 01-2119471836-27	0.1 - 1	Ox. Sol. 3, H272 Acute Tox. 3 (Oral), H301 Eye Irrit. 2, H319 Aquatic Acute 1, H400

#### **Specific concentration limits:**

Name	Product identifier	Specific concentration limits
BENZISOTHIAZOLINONE	(CAS-No.) 2634-33-5 (EC-No.) 220-120-9 (EC Index-No.) 613-088-00-6	(C >= 0.05) Skin Sens. 1, H317

Full text of H-statements: see section 16

## **SECTION 4: First aid measures**

### 4.1. Description of first aid measures

First-aid measures general : Get medical advice/attention if you feel unwell.

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. If experiencing respiratory

symptoms: Get medical advice/attention.

First-aid measures after skin contact : Wash skin with plenty of water. If skin irritation or rash occurs: Get medical advice/attention.

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to

do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

First-aid measures after ingestion : Rinse mouth. Do not induce vomiting. Get medical advice/attention if you feel unwell.

## 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation : Not expected to present a significant inhalation hazard under anticipated conditions of normal

use.

Symptoms/effects after skin contact : May cause an allergic skin reaction.

Symptoms/effects after eye contact : Causes serious eye irritation. redness, itching, tears.

Symptoms/effects after ingestion : Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## **SECTION 5: Firefighting measures**

#### 5.1. Extinguishing media

Suitable extinguishing media : Foam. Carbon dioxide. Dry powder.

Unsuitable extinguishing media : Do not use water jet.

### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Extremely flammable aerosol.

Explosion hazard : Pressurised container: May burst if heated.

Reactivity in case of fire : Not known.

23/11/2018 EN (English) 2/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Hazardous decomposition products in case of

: Toxic fumes may be released. Carbon dioxide. Carbon monoxide.

#### Advice for firefighters

Precautionary measures fire

: Evacuate area.

Firefighting instructions

: Eliminate all ignition sources if safe to do so. Fight fire with normal precautions from a

reasonable distance. Exercise caution when fighting any chemical fire.

Protection during firefighting

Do not attempt to take action without suitable protective equipment. Self-contained breathing

apparatus. Complete protective clothing.

## **SECTION 6: Accidental release measures**

#### Personal precautions, protective equipment and emergency procedures

General measures

: Ensure adequate ventilation. Eliminate all ignition sources if safe to do so. Avoid release to the environment.

#### 6.1.1. For non-emergency personnel

Protective equipment

Wear recommended personal protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

**Emergency procedures** 

Ventilate spillage area. Eliminate all ignition sources if safe to do so. Avoid contact with skin and eyes.

#### 6.1.2. For emergency responders

Protective equipment

Emergency procedures

: Wear recommended personal protective equipment. For further information refer to section 8:

"Exposure controls/personal protection".

: Ventilate area. Avoid contact with skin and eyes. Eliminate all ignition sources if safe to do so.

#### **Environmental precautions** 6.2.

Avoid release to the environment.

#### Methods and material for containment and cleaning up 6.3.

For containment

: Collect all waste in suitable and labelled containers and dispose according to local legislation.

Methods for cleaning up

Wear personal protective clothing (see chapter 8). Stop leak if safe to do so. Wipe up with absorbent material (for example cloth). Place in a suitable container for disposal in accordance with the waste regulations (see Section 13).

Other information

: Dispose of materials or solid residues at an authorized site.

#### Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of solid materials or residues refer to section 13: "Disposal considerations".

# **SECTION 7: Handling and storage**

## Precautions for safe handling

Precautions for safe handling

: Observe the label precautions. Keep out of reach of children. Ensure adequate ventilation, especially in confined areas. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Wear personal protective equipment. Avoid contact with skin

Hygiene measures

Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

#### Conditions for safe storage, including any incompatibilities

Technical measures

: Ensure adequate ventilation, especially in confined areas.

Storage conditions

Storage area

Keep out of reach of children. Store in a well-ventilated place. Keep cool. Do not expose to temperatures exceeding 50 °C/ 122 °F. Protect from sunlight. Keep away from ignition sources.

Store in a well-ventilated place.

## Specific end use(s)

Automotive Care Products.

## SECTION 8: Exposure controls/personal protection

### **Control parameters**

No additional information available

#### **Exposure controls**

Appropriate engineering controls

: Ensure adequate ventilation, especially in confined areas.

Personal protective equipment

: Wear recommended personal protective equipment.

23/11/2018 EN (English) 3/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Materials for protective clothing : Wear suitable protective clothing

Hand protection : Wear chemically resistant protective gloves.

Eye protection : Wear safety glasses with side shields. Eye protection should only be necessary where liquid

could be splashed or sprayed

Skin and body protection : Wear suitable protective clothing

Respiratory protection : Not required for normal conditions of use

Environmental exposure controls : Avoid release to the environment.

Consumer exposure controls : Read label before use. Observe the label precautions.

Other information : Do not eat, drink or smoke when using this product.

## **SECTION 9: Physical and chemical properties**

### 9.1. Information on basic physical and chemical properties

Physical state : Liquid

Colour : No data available Odour · characteristic Odour threshold : No data available No data available рΗ Relative evaporation rate (butylacetate=1) : No data available Melting point : Not applicable Freezing point : No data available No data available Boiling point Flash point No data available : No data available Auto-ignition temperature Decomposition temperature : No data available

Flammability (solid, gas) : Extremely flammable aerosol.

Vapour pressure : No data available Relative vapour density at 20 °C : No data available Relative density : No data available

Solubility : Miscible.

Log Pow : No data available
Viscosity, kinematic : No data available
Viscosity, dynamic : No data available

Explosive properties : Pressurised container: May burst if heated.

Oxidising properties : Non oxidizing.

Explosive limits : No data available

## 9.2. Other information

VOC content : 10 %

# SECTION 10: Stability and reactivity

## 10.1. Reactivity

Extremely flammable aerosol. Pressurised container: May burst if heated.

## 10.2. Chemical stability

Stable under normal conditions.

# 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

#### 10.5. Incompatible materials

Acids. Oxidising agents.

## 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

23/11/2018 EN (English) 4/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

	SECTION	11: Toxico	logical i	nformation
--	---------	------------	-----------	------------

## 11.1. Information on toxicological effects

Acute toxicity : Not classified

BENZISOTHIAZOLINONE (2634-33-5)	
LD50 oral	1020 mg/kg bodyweight
LD50 dermal	4115 mg/kg bodyweight
LC50 inhalation rat (Dust/Mist - mg/l/4h)	100 mg/l/4h

#### sodium nitrite (7632-00-0)

LD50 oral 180 mg/kg bodyweight

Skin corrosion/irritation : Not classified

Serious eye damage/irritation : Causes serious eye irritation.

Respiratory or skin sensitisation : May cause an allergic skin reaction.

Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified
STOT-single exposure : Not classified
STOT-repeated exposure : Not classified
Aspiration hazard : Not classified

TYRE FOAM
-----------

Vaporizer Aerosol

## **SECTION 12: Ecological information**

#### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse

effects in the environment.

Ecology - water : No data available on ecotoxicity.

BENZISOTHIAZOLINONE (2634-33-5)	
LC50 fish 1	2.18 mg/l
EC50 Daphnia 1	0.99 mg/l
EC50 other aquatic organisms 1	2.94 mg/l EC50 waterflea (48 h)
EC50 other aquatic organisms 2	0.11 mg/l IC50 algea (72 h) mg/l
sodium nitrite (7632-00-0)	
LC50 fish 1	0.54 mg/l
EC50 other aquatic organisms 1	15.4 mg/l EC50 waterflea (48 h)

## 12.2. Persistence and degradability

TYRE FOAM	
Persistence and degradability	No data available.

#### 12.3. Bioaccumulative potential

TYRE FOAM	
Bioaccumulative potential	No data available.

## 12.4. Mobility in soil

TYRE FOAM	
Ecology - soil	No data available.

#### 12.5. Results of PBT and vPvB assessment

No additional information available

# 12.6. Other adverse effects

Other adverse effects : None known.

Additional information : Avoid release to the environment.

# **SECTION 13: Disposal considerations**

## 13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

23/11/2018 EN (English) 5/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Product/Packaging disposal recommendations

Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation. Do not pierce or burn, even after

## **SECTION 14: Transport information**

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
1950	1950	1950	1950	1950
14.2. UN proper shippin	g name			
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
Transport document descri	ption			
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1			
14.3. Transport hazard	class(es)			
2.1	2.1	2.1	2.1	2.1
2	2	2	2	2
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental haz	zards			
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
	No supplementary information available			

#### 14.6. Special precautions for user

#### - Overland transport

Classification code (ADR) : 5F

Special provisions (ADR) : 190, 327, 344, 625

Limited quantities (ADR) : 11 Excepted quantities (ADR) : E0

Packing instructions (ADR) : P207, LP02 : PP87, RR6, L2 Special packing provisions (ADR)

Mixed packing provisions (ADR) : MP9 Transport category (ADR) : 2 Special provisions for carriage - Packages : V14 (ADR)

Special provisions for carriage - Loading,

: CV9, CV12

unloading and handling (ADR)

Special provisions for carriage - Operation : S2

(ADR)

: D Tunnel restriction code (ADR)

- Transport by sea

: 63, 190, 277, 327, 344, 959 Special provisions (IMDG)

: None

: 126

Limited quantities (IMDG) : SP277 Excepted quantities (IMDG) : E0 Packing instructions (IMDG) : P207, LP02 : PP87, L2 Special packing provisions (IMDG) EmS-No. (Fire) : F-D EmS-No. (Spillage) : S-U

- Air transport

MFAG-No

Stowage category (IMDG)

PCA Excepted quantities (IATA) : E0 PCA Limited quantities (IATA) : Y203

23/11/2018 EN (English) 6/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

PCA limited quantity max net quantity (IATA) : 30kgG
PCA packing instructions (IATA) : 203
PCA max net quantity (IATA) : 75kg
CAO packing instructions (IATA) : 203
CAO max net quantity (IATA) : 150kg

Special provisions (IATA) : A145, A167, A802

ERG code (IATA) : 10L

- Inland waterway transport

Classification code (ADN) : 5F

Special provisions (ADN) : 190, 327, 344, 625

Limited quantities (ADN) : 1 L

Excepted quantities (ADN) : E0

Equipment required (ADN) : PP, EX, A

Ventilation (ADN) : VE01, VE04

Number of blue cones/lights (ADN) : 1
Carriage prohibited (ADN) : No
Not subject to ADN : No

- Rail transport

Classification code (RID) : 5F

Special provisions (RID) : 190, 327, 344, 625

Limited quantities (RID) : 1L Excepted quantities (RID) : E0

Packing instructions (RID) : P207, LP02 Special packing provisions (RID) : PP87, RR6, L2

Mixed packing provisions (RID): MP9Transport category (RID): 2Special provisions for carriage – Packages: W14

(RID)

Special provisions for carriage - Loading,

unloading and handling (RID)

: CW9, CW12

Colis express (express parcels) (RID) : CE2
Hazard identification number (RID) : 23
Carriage prohibited (RID) : No

## 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

## **SECTION 15: Regulatory information**

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

VOC content : 10 %

Detergent Regulation: Ingredient data sheet:

Component	CAS-No.	%
AQUA	7732-18-5	>=10%
Butane n-	106-97-8	1 - 10%
Isobutane	75-28-5	1 - 10%
PROPANE	74-98-6	1 - 10%
Longchain alkoxylated alcohol C10 polymer	166736-08-9	1 - 10%
Longchain alkoxylated C10 polymer	166736-08-9	1 - 10%
BENZOIC ACID, SODIUM BENZOATE	532-32-1	0.1 - 1%
BENZISOTHIAZOLINONE	2634-33-5	0.1 - 1%
TRIETHANOLAMINE	102-71-6	0.1 - 1%
SODIUM NITRITE	7632-00-0	0.1 - 1%

23/11/2018 EN (English) 7/8

# Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

DIETHANOLAMINE	111-42-2	<0.1%
AMMONIUM HYDROXIDE	1336-21-6	<0.1%
Detergent Regulation : Labelling of contents:		·
Component		%
BENZISOTHIAZOLINONE		
BENZOIC ACID, SODIUM BENZOATE		

#### 15.1.2. National regulations

Seveso Directive: 2012/18/EU (Seveso III)

#### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## **SECTION 16: Other information**

Other information

: This information of the Safety Data Sheet is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product. We are not responsible for the correctness of the information provided and any consequences in using it. Please read the SDS carefully before using the product.

#### Full text of H- and EUH-statements:

Tail text of 11 and Eo11 statements.	
Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aerosol 1	Aerosol, Category 1
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Ox. Sol. 3	Oxidising Solids, Category 3
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H272	May intensify fire; oxidiser.
H301	Toxic if swallowed.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H400	Very toxic to aquatic life.

#### SDS EU TURTLEWAX

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product

23/11/2018 EN (English) 8/8