## FXPL002



- Fill-level measurement in all media: liquid, pasty, sticky or solid
- Process optimization with IO-Link 1.1
- Quick sensor replacement with data storage
- Two adjustable switching outputs

LevelTech fill-level sensors work in accordance with the innovative frequency sweep principal. With the help of this functional principle, the sensors detect any desired medium on the basis of the measured resonant frequency. With their two adjustable switching outputs, the sensors are capable of differentiating between foam and liquid or two different media. Sensor parameters, as well as filter and output functions, can be individually configured via IO-Link. The stainless steel housing is FDA compliant and can be installed in the tightest of spaces thanks to its compact design.



Sensor-specific data	
Measuring principle	Frequency sweep
Measuring Range	DK > 1,5
Medium	Liquids, granulate, powder
Response Time	0,04 s
Environmental conditions	
Media temperature TM (TU < 50 °C)	-40115 °C
Media temperature TM brief	-40130 °C
(TU < 50 °C, t < 1 h) Ambient temperature	-4085 °C
Storage temperature	-4085 °C
Pressure Resistance	100 bar
EMC	DIN EN 61326 *
Vibration resistance per DIN IEC 60068-2-6	1,6 mm p-p (225 Hz) 4 a (25100 Hz)
Electrical Data	4 d (25100 HZ)
Supply Voltage	836 V DC
Current Consumption (Ub = 24 V)	< 35 mA
Number of Switching Outputs	2
Power-up Time	< 3 s
Switching Output/Switching Current	100 mA
Switching Output Voltage Drop	< 0.7 V
Leakage Current	< 100 μA
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Interface	IO-Link V1.1
Mechanical Data	
Setting Method	Teach-in/IO-Link
Housing Material	1.4404
Material in contact with media	PEEK Natura 1.4404
Degree of Protection	IP67/IP69K
Connection	M12 × 1; 4-pin
Connector Plug Material	Polycarbonate
Process Connection	1/2" NPT
Safety-relevant Data	
MTTFd (EN ISO 13849-1)	686 a
Function	
Attenuation (adjustable)	010 s
Selective fill-level measurement	yes
Configurable as PNP/NPN/Push-Pull	
Switchable to NC/NO	
IO-Link	
Connection Diagram No.	704
Suitable Connection Equipment No.	2

<sup>\*</sup> mounted in closed metal tank

## **Complementary Products**

IO-Link Master

Software

















