

1300 Henley Court Pullman, WA 99163 509.334.6306 www.digilentinc.com

PmodR2R[™] Reference Manual

Revised February 13, 2015 This manual applies to the PmodR2R rev. B

Overview

The Digilent PmodR2R is an 8-bit Digital-to-Analog converter. It may not look as sleek and professional as some of the other DACs that are out there, but on a fundamental level that is easy to see, this Pmod does exactly the same thing as its counterparts.



Features include:

- 8-bit digital to analog conversion at up to 25MHz
- Easy attachment of oscilloscopes to illustrate the data conversion process

The PmodR2R.

1 Functional Description

The PmodR2R accepts 8 bits in parallel, either at a logic low or high voltage, which then go through a resistor ladder to output a desired voltage. The "R2R" resistor ladder is one of the most popular ways that digital-to-analog converters take a set of digital inputs and create a single analog output, requiring just two resistor values of R and 2^{R} . Because this Pmod only uses 10K Ω and 20K Ω resistors, very little current is drawn from the input pins.

2 Interfacing with the Pmod

The PmodR2R communicates with the host board via the GPIO protocol. Each of the 8 input pins are expected to send out either a logic high or logic low voltage signal in such a way that represents the desired binary ratio of the full analog output.

DOC#: 502-165



Header J1			
Pin Number (top row)	Description	Pin Number (bottom row)	Description
1	Data Bit 0	7	Data Bit 4
2	Data Bit 1	8	Data Bit 5
3	Data Bit 2	9	Data Bit 6
4	Data Bit 3	10	Data Bit 7
5	Ground	11	Ground
6	VCC	12	VCC

Table 1. Pinout description table.

3 Physical Dimensions

The pins on the pin header are spaced 100 mil apart. The PCB is 1 inch long on the sides parallel to the pins on the pin header and 0.8 inches long on the sides perpendicular to the pin header.