### **Jalas**®







SIZE	ART. NO.	EAN NO.
36	1738-36	6408487501432
37	1738-37	6408487501449
38	1738-38	6408487501456
39	1738-39	6408487501463
40	1738-40	6408487501470
41	1738-41	6408487501487
42	1738-42	6408487501494
43	1738-43	6408487501500
44	1738-44	6408487501517
45	1738-45	6408487501524
46	1738-46	6408487501531
47	1738-47	6408487501548

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

# JALAS® 1738 ZENIT EASYROLL

EN ISO 20345:2011, S3 SRC

#### **PROPERTIES**

Highest level of protection, excellent grip, perfect fit, extra comfortable, excellent shock absorption

#### **SPECIFICATION**

TYPE OF SHOE Safety footwear, low shoes

 $\label{eq:protection} \mbox{MATERIAL Plasma-treated composite} \\ \mbox{(PTC) textile} \\$ 

FITTING Regular

SIZE RANGE 36-47

**COLLECTION Zenit** 

PLATFORM Zenit

UPPER MATERIAL PU-coated leather, split leather

PRONOSE MATERIAL PU

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester, polyamide

SOLE MATERIAL PU midsole, plastic shank, RPU outsole

INSOLE FX2 Supreme

INSOLE MATERIAL Textile, soft EVA, polyester-based conductive thread, merino wool, double shock absorption zones in Poron® XRD®

FASTENING Boa®

COLOUR Black, grey, red





### **Jalas**®



### ( (



Aluminium toecap



Anti-static properties



Nail protection in plasma-treated composite (PTC) textile



ESD



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



Ergothan Shock Absorption System



Stabilizator

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

## JALAS® 1738 ZENIT EASYROLL

#### **FEATURES**

ProNose toe reinforcement, oil-resistant outsole, anti-static properties, polstered shaft edge, ventilating insole, Boa® closure system, quick-tie, stabilizator, water repellent, double shock absorption zones, conforms with IEC 61340-5-1 (ESD)

#### **PRIMARY PROTECTION**

Prevents risk of:, toe injuries, nail penetration, antistatic

#### **PRIMARY ENVIRONMENTS OF USE**

Outdoors, environments with risk for outsole penetration



#### **EJENDALS AB**

Box 7, SE-793 21 Leksand, Sweden Phone +46 (0) 247 360 00 Fax +46 (0) 247 360 10

> info@ejendals.com order@ejendals.com

> > www.ejendals.com

### **Jalas**®



### CE



Aluminium toecap



Anti-static properties



Nail protection in plasma-treated composite (PTC) textile



ESD



Water repellent



Oil-resistant outsole



ProNose toe reinforcement



Ergothan Shock Absorption System



Stabilizator

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

## JALAS® 1738 ZENIT EASYROLL

COMPLIANCE EN ISO 20345:2011

#### **COMPLIANCE DESCRIPTION**

SB: Footwear with toe protection tested with 200 J impact and 15kN compression force (includes oil resistant outsole)

S1: Footwear made from leather and other materials excluding all-rubber or all-polymeric footwear + closed seat region + SB + A + E

S2: S1 + WRU

S3: S2 + P

WRU: Water-resistant upper

P: Penetration-resistant outsole

A: Electrical resistance (between 0.1-1000 Mega Ohms

E: Energy absorption in the heel area (tested at 20 Joules)

SRA: Slip-resistance on ceramic tile floor with Sodium lauryl sulphate solution

SRB: Slip-resistance on steel floor with glycerol

SRC: SRA + SRB

IEC 61340-5-1: Electrostatic Discharge (ESD) resistance below 35 megaohm

BGR 191: Orthopedic footwear adjustment according to German BGR 191. Footwear is tested with adjusted orthopedic insoles in accordance with EN ISO 20345 standard



**EJENDALS AB** 

Box 7, SE-793 21 Leksand, Sweden
Phone +46 (0) 247 360 00
Fax +46 (0) 247 360 10

info@ejendals.com order@ejendals.com

www.ejendals.com