



Fußgerechte Sicherheit

From range: Baak Sports light

Article 71462 Rick 2 Half shoe S1P SRC ESD





Certified for orthopaedic insocks Details under www.baak.de/en

BAAK go relax system

natural bending line

flex zone in ball area

mmonummunummunum

foot fitting instead of straight



Knee- & Backfriendly Scientically evaluated Foot confrom fitting & function

Abrasion resistant microfiber material with breathable **Upper**

textile inserts, softly padded edge

climate-regulating textile lining Tongue: closed, padded, with attachment loop

Lacing: round laces black/yellow

Closing parts: textile loops and metal-free eyelets

Insock Soft damping Baak ESD softstep-insock, breathable with

high humidity absorption, antibacterial, fungicide

(article 4662)

Outsole EVA/nitrile sole with **flex zone** in the ball section

> EVA midsole with high energy absorption, damping impact for joints, knees and spine due to its full surface damping;

nitrile outsole: robust, slip resistant (SRC)

Toecap Wide composite flex cap

Anti-Penetration Non-metallic, anti-penetration, flexible insole board

Plus Baak® go@relax system

> Consisting of flex zone, flex cap and H-element for a foot fitting bending. Scientifically proofed positive effects on

joints and spine

Sizes/Width 36-40 / 10,5 and 41-50 / 12

Weight Approx. 550 gr.per piece (size 42)

Designation According to EN ISO 20345 S1P SRC ESD

Examples for use Areas, where the impact of humidity is not to be expected: Automotive sector, electronic

industry, printing industry, energy industry, packing industry, logistics, aviation sector,

administration

Baak GmbH & Co. KG Hubertusstrasse 3 D-47638 Straelen

Phone: +49/2834/942 41-0 Fax: +49/2834/942 41-69

Email: info@baak.de Internet: www.baak.de/en

